

Perform-X Hi-Lo Radiographic System

Control-X Medical advanced diagnostic systems

The Perform-X Hi-Lo radiographic system from Control-X Medical represents a unique performance-price ratio in the industry, high level of quality, durability, great values and comfort in diagnostic x-ray imaging systems today. As a special package for the healthcare community, the Perform-X Hi-Lo system represents an affordable choice with no compromises for the imaging specialist.

WS 99 wallstand

- High speed bucky operation
- Extended travel to the floor
- Smooth and precise operation through the special bearing system of the carriage
- Eye-catching design

Phoenix Hi-Lo four-way table

- Heavy-duty, yet graceful design offers convenient vertical height adjustment
- Four-way effortless positioning
- Standard high-speed bucky operation
- Extremely low tabletop filtration
- Standard high-speed bucky operation

**System shown with the
50 kW PCX 650HF¹⁰⁰
(100 kHz) high
frequency generator**



TS 99 tubestands

- Heavy-duty precision
- Freestanding or floor-to-ceiling or floor-to-wall operation provide for maximum safety and comfort
- Optional column rotation and cross-table travel ensure that the TS 99 tubestands are the right components for your imaging procedures
- Extremely low floor positioning allows easy lower extremity exposure
- Simple installation made possible with the heavy-duty dual floor rail system
- Precision bearing systems provide “no-slope”-operation on all travels

Control-X generators

A variety of high frequency generators support top quality exposures for all applications.

Digital capability

The Perform-X Hi-Lo system is compatible with a large number of CR or DR detectors and can be ordered with different digital options.



cxmed.com

Perform-X System

Control-X Medical Advanced Diagnostic Systems

The Perform-X radiographic system from Control-X Medical represents the highest level of quality, durability and value in diagnostic x-ray imaging systems. These systems are available as a special package for the healthcare community. The performance-price ratio is unique in the industry.

WS 99 wallstand

- High speed bucky operation
- Extended travel to the floor
- Smooth and precise operation through the special bearing system of the carriage

TS 99 tubestand

- Heavy-duty precision tube stand
- Freestanding or floor-to-ceiling or floor-to-wall operation
- Optional column rotation and cross-table travel
- Extremely low floor positioning ensures easy lower extremity exposures
- Easy installation with the heavy-duty floor rail system
- Precision bearing systems provide "no-slope"-operation on all travels



Control-X generators

- State of the art high frequency generators ensure high quality exposures in the full radiographic range.
- 125 or 150 kV maximum tube voltage for full kV coverage
- Automatic Exposure Control (AEC) and anatomical programs (both optional) will guarantee perfect exposure parameters for all applications

Stylix four-way table

- Heavy-duty four-way radiographic table with easy operation
- Dual braking system (for longitudinal and cross-table travel)
- Foot switch control ensures comfortable patient positioning
- Extremely low filtration tabletop
- Standard high-speed bucky operation



System shown
with the
MS 550HF (40 kW)
high frequency
generator